

Vacuum suction cup holder ESH-HE-2-M5

Part number: 189254

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	2 mm
Volume	0.036 cm ³
Mounting position	Any
Structural design	Vacuum connection at top
Classification of suction cup holder	Size 2
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	3 g
Type of mounting	With external thread Via vacuum connection
Suction cup mounting	Diameter: 4 mm
Vacuum connection	M5
Note on materials	RoHS compliant
Seals material	Wrought aluminum alloy NBR POM Steel
Retainer bracket material	Quenched and tempered steel