

# Vacuum suction cup holder ESH-HF-2-M10X1

Part number: 189261

FESTO



 [General operating condition](#)

## Data sheet

| Feature                               | Value  |
|---------------------------------------|--|
| Suction cup holder height compensator | 2.6 mm   |
| Nominal width                         | 2 mm   |
| Volume                                | 0.09 cm <sup>3</sup>                                 |
| Mounting position                     | Vertical   |
| Structural design                     | Vacuum connection at top<br>with height compensation |
| Classification of suction cup holder  | Size 2   |
| Operating medium                      | Atmospheric air based on ISO 8573-1:2010 [7::-]      |
| Corrosion resistance class (CRC)      | 1 - Low corrosion stress                             |
| LABS (PWIS) conformity                | VDMA24364-A1-L                                       |
| Ambient temperature                   | -10 °C ... 60 °C                                     |
| Product weight                        | 14 g   |
| Type of mounting                      | With external thread<br>Via vacuum connection        |
| Suction cup mounting                  | Diameter 4 mm  |
| Vacuum connection                     | M10x1  |
| Note on materials                     | RoHS-compliant                                       |
| Seals material                        | NBR<br>POM   |
| Retainer bracket material             | Tempered steel                                       |