

# Vacuum suction cup holder ESH-HF-4-M14X1

Part number: 189263

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Suction cup holder height compensator	6 mm
Nominal width	4 mm
Volume	0.655 cm <sup>3</sup>
Mounting position	Vertical
Structural design	Vacuum connection at top with height compensation
Classification of suction cup holder	Size 4
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	52 g
Type of mounting	With external thread Via vacuum connection
Suction cup mounting	M6
Vacuum connection	M14x1
Note on materials	RoHS-compliant
Seals material	NBR POM
Retainer bracket material	Tempered steel