

Vacuum suction cup holder ESH-HF-4-M14X1

Part number: 189263

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Suction cup holder height compensator	6 mm
Nominal width	4 mm
Volume	0.655 cm ³
Mounting position	Vertical
Structural design	Vacuum connection at top with height compensation
Classification of suction cup holder	Size 4
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	52 g
Type of mounting	With external thread Via vacuum connection
Suction cup mounting	M6
Vacuum connection	M14x1
Note on materials	RoHS compliant
Seals material	NBR POM
Retainer bracket material	Quenched and tempered steel