

Vacuum suction cup ESS-200-SS

Part number: 189332

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Min. workpiece radius	680 mm
Nominal width	10 mm
Suction cup diameter	200 mm
Suction cup volume	245.454 cm ³
Connection position	up
Mounting position	Any
Symbol	00991485
Classification of suction cup holder	Size 6
Suction cup shape	Round, flat
Operating pressure	-0.095 MPa ... 0 MPa
Operating pressure	-0.95 bar ... 0 bar
Operating pressure	-13.775 psi ... 0 psi
Nominal operating pressure	-0.07 MPa
Nominal operating pressure	-0.7 bar
Nominal operating pressure	-10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
For use in the food industry	See supplementary material information
Ambient temperature	-30 °C ... 180 °C
Holding force at nominal operating pressure	1610 N
Lateral force at nominal operating pressure	425 N
Product weight	1198 g
Type of mounting	Via vacuum connection
Vacuum connection	M20x2
Color	Transparent
Shore hardness	50 +/-5
Material of screwed plug	NBR Steel, nickel-plated Steel, galvanized and chrome-plated
Note on materials	RoHS compliant

Feature	Value
Suction cup material	VMQ (silicone)