

# Push-in fitting, self-sealing QSMK-1/4-1/4-U

Part number: 190712

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	Mini
Nominal width	3 mm
Type of seal on screwed plug	Coating
Mounting position	Any
Design	Straight design
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating pressure for entire temperature range	-13.775 psi ... 145 psi
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque	14 Nm
Product weight	24 g
Type of mounting	External hexagon 9/16
Pneumatic connection 1	external thread 1/4 NPT
Pneumatic connection 2	for pneumatic tubing outer diameter 1/4"
Ambient temperature Fahrenheit	14 °F ... 140 °F
Releasing ring color	Gray
Note on materials	RoHS compliant
Housing material	Brass Nickel-plated
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	high-alloy stainless steel