

Multiple distributor QSLV3-3/8-3/8-U

Part number: 190785

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal width | 5.3 mm |
| Type of seal on screwed plug | Coating |
| Mounting position | Any |
| Structural design | Push-pull principle |
| Pack size | 1 |
| Operating pressure for entire temperature range | -0.095 MPa ... 1 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 145 psi |
| Maritime classification | See certificate |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. tightening torque | 24 Nm |
| Product weight | 103 g |
| No. of outlets | 3 |
| No. of supply lines | 1 |
| Pneumatic connection 1 | external thread 3/8 NPT |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 3/8" |
| Ambient temperature Fahrenheit | 14 °F ... 140 °F |
| Releasing ring color | Gray |
| Material of screwed plug | Brass, nickel-plated |
| Note on materials | RoHS-compliant |
| Housing material | PBT |
| Releasing ring material | POM |
| Material of tubing seal | NBR |
| Material of tube retaining claw | High-alloy stainless steel |