

Non return valve H-QSM-5/32-U

Part number: 190841

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Valve function | Non-return function |
| Pneumatic connection 1 | QS-5/32 |
| Pneumatic connection 2 | QS-5/32 |
| Type of mounting | Line installation |
| Normal nominal flow rate (normalized to DIN 1343) | 139 l/min |
| Operating pressure | -1 bar ... 10 bar |
| Ambient temperature | 0 °C ... 60 °C |
| Housing material | Aluminum |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Symbol | 00991455 |
| Min. differential pressure, opening | 0.1 bar |
| Min. differential pressure, closing | 0.2 bar |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 5.3 g |
| Note on materials | RoHS-compliant |