

Pressure gauge PAGL-HP3-63-60-G14-RC

Part number: 1908519

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Display range	0 bar ... 60 bar
Display range	0 MPa ... 6 MPa
Display range	0 psi ... 870 psi
Symbol	00991463
Conforms to standard	EN 837-1
Pressure gauge nominal size	63
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Structural design	Bourdon tube pressure gauge
Type of mounting	Line installation
Operating medium	Inert gas Neutral liquids
Information on operating and pilot media	No acetylene No oxygen
Operating pressure	0 MPa ... 6 MPa
Operating pressure	0 bar ... 60 bar
Operating pressure	0 psi ... 870 psi
Intermittent load factor	0.66
Measurement accuracy class	1.6
Degree of protection	IP65
Storage temperature	-40 °C ... 70 °C
Temperature of medium	0 °C ... 60 °C
Ambient temperature	0 °C ... 60 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Connection position	Radial at bottom
Pneumatic connection	G1/4
Materials in contact with the media	Brass
Material of screwed plug	Brass
Housing material	Steel

Feature	Value
Inspection window material	PS
Housing colour	Silver
Product weight	80 g
Scale	Triple scale MPa (external) bar (außen) psi (internal)