


# Non return valve HB-10-32-UNF-QSM-5/32-U

Part number: 190857

FESTO



## Data sheet

 [General operating condition](#)

Feature	Value
Valve function	Non-return function
Pneumatic connection 1	QS-5/32
Pneumatic connection 2	10-32 UNF-2A
Type of mounting	Screw-in
Normal nominal flow rate (normalized to DIN 1343)	145 l/min
Operating pressure	-1 bar ... 10 bar
Ambient temperature	0 °C ... 60 °C
Housing material	Brass
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Symbol	00991455
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Product weight	7.2 g
Note on materials	RoHS-compliant