

Vacuum cup without connector ESV-30-CN

Part number: 191073

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|---|
| Suction cup height compensation | 10.5 mm |
| Min. workpiece radius | 80 mm |
| Suction cup diameter | 30 mm |
| Suction cup volume | 9.47 cm ³ |
| Connection position | up |
| Mounting position | Any |
| Symbol | 00991485 |
| Suction cup shape | round protective bellows 3.5-fold |
| Operating pressure | -0.095 MPa ... 0 MPa |
| Operating pressure | -0.95 bar ... 0 bar |
| Operating pressure | -13.775 psi ... 0 psi |
| Nominal operating pressure | -0.07 MPa |
| Nominal operating pressure | -0.7 bar |
| Nominal operating pressure | -10.15 psi |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| For use in the food industry | See supplementary material information |
| Ambient temperature | -10 °C ... 70 °C |
| Holding force at nominal operating pressure | 20.8 N |
| Product weight | 5.8 g |
| Color | Black |
| Shore hardness | 50 +/-5 |
| Note on materials | RoHS compliant |
| Suction cup material | NBR |