

# Vacuum filter ESF-3

Part number: 191202

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
Grade of filtration	10 µm
Symbol	00991483
Operating pressure	-0.95 bar ... 4 bar
Flow rate at negative pressure = -0.75 bar	100 l/min
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C ... 60 °C
Product weight	9 g
Type of mounting	With external thread Via vacuum connection
Pneumatic connection	M4
Vacuum connection	M4
Note on materials	RoHS compliant
Seals material	NBR
Compressed air filter material	PVF
Housing material	Aluminum Brass, nickel-plated