

Vacuum filter ESF-4B

Part number: 191204

FESTO



[PDF](#) [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Mounting position | Any |
| Grade of filtration | 10 µm |
| Symbol | 00991483 |
| Operating pressure | -0.95 bar ... 4 bar |
| Flow rate at negative pressure = -0.75 bar | 270 l/min |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:-:-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Ambient temperature | 0 °C ... 60 °C |
| Product weight | 19 g |
| Type of mounting | With external thread Via vacuum connection |
| Pneumatic connection | M6 |
| Vacuum connection | M6 |
| Note on materials | RoHS compliant |
| Seals material | NBR |
| Compressed air filter material | PVF |
| Housing material | Aluminum Brass, nickel-plated |