

# Angle compensator ESWA-3

Part number: 191205

FESTO



 [General operating condition](#)

## Data sheet

| Feature                              | Value                            |
|--------------------------------------|----------------------------------|
| Angle compensator +/-                | 15 deg                           |
| Mounting position                    | Any                              |
| Structural design                    | Ball joint                       |
| Classification of suction cup holder | Size 3                           |
| Operating pressure                   | -0.95 bar ... 4 bar              |
| Corrosion resistance class (CRC)     | 1 - Low corrosion stress         |
| LABS (PWIS) conformity               | VDMA24364-A1-L                   |
| Ambient temperature                  | 0 °C ... 60 °C                   |
| Product weight                       | 9 g                              |
| Type of mounting                     | With external thread             |
| Suction cup mounting                 | M4                               |
| Pneumatic connection                 | M4                               |
| Note on materials                    | RoHS-compliant                   |
| Seals material                       | NBR                              |
| Housing material                     | Aluminum<br>Brass, nickel-plated |