

Angle compensator ESWA-5

Part number: 191207

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Angle compensator +/-	15 deg
Mounting position	Any
Structural design	Ball joint
Classification of suction cup holder	Size 5
Operating pressure	-0.95 bar ... 4 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C ... 60 °C
Product weight	57 g
Type of mounting	With external thread
Suction cup mounting	M10
Pneumatic connection	M10
Note on materials	RoHS compliant
Seals material	NBR
Housing material	Aluminum Brass, nickel-plated