


Service unit LFR-1/2-D-DI-MAXI-KE-A

Part number: 192458

FESTO



[PDF General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|---|
| Size | Maxi |
| Series | D |
| Actuator lock | Rotary knob with detent |
| Mounting position | Vertical $\pm 5^\circ$ |
| Grade of filtration | 40 μm |
| Condensate drain | Fully automatic |
| Structural design | Branching module Pressure switch Filter regulator with pressure gauge |
| Max. condensate volume | 43 ml |
| Bowl guard | Metal bowl guard |
| Symbol | 00991778 |
| Pressure gauge | with pressure gauge |
| Operating pressure | 0.2 MPa ... 1.2 MPa |
| Operating pressure | 2 bar ... 12 bar |
| Operating pressure | 29 psi ... 174 psi |
| Pressure regulation range MPa | 0.05 MPa ... 1.2 MPa |
| Pressure regulation range | 0.5 bar ... 12 bar |
| Pressure regulation range psi | 7.25 psi ... 174 psi |
| Operating medium | Inert gases |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gases |
| Temperature of medium | -10 $^\circ\text{C}$... 60 $^\circ\text{C}$ |
| Ambient temperature | -10 $^\circ\text{C}$... 60 $^\circ\text{C}$ |
| Product weight | 2600 g |
| Type of mounting | With accessories |
| Pneumatic connection 1 | G1/2 |
| Pneumatic connection 2 | G1/2 |
| Housing material | Die-cast zinc |
| Material of bowl | PC |