

Filter LF-D-5M-MAXI

Part number: 192559

FESTO



 General operating condition

Data sheet

| Feature | Value |
|----------------------------------|--|
| Size | Maxi |
| Series | D |
| Mounting position | Vertical $\pm 5^\circ$ |
| Grade of filtration | 5 μm |
| Condensate drain | Manual, rotating |
| Structural design | Sinter filter with centrifugal separator |
| Bowl guard | Metal bowl guard |
| Symbol | 00991519 |
| Operating pressure | 0 bar ... 16 bar |
| Operating medium | Inert gases |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 °C ... 60 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gases |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Type of mounting | With accessories |
| Pneumatic connection 1 | Sub-base |
| Pneumatic connection 2 | Sub-base |
| Note on materials | RoHS compliant |
| Compressed air filter material | Protective grounding |
| Housing material | Die-cast zinc |
| Material of bowl | PC |