

# Blanking plug CQC-28H

Part number: 194590

FESTO



 [General operating condition](#)

## Data sheet

| Feature   | Value  |
|---|--|
| Mounting position                               | Any  |
| Pack size                                       | 1  |
| Structural design                               | Push-pull principle  |
| Operating pressure for entire temperature range | -0.95 bar ... 7 bar  |
| Temperature-dependent operating pressure        | -0.95 bar ... 15 bar   |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-]                      |
| Information on operating and pilot media        | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)                | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                          | VDMA24364 Zone III   |
| For use in the food industry                    | See supplementary material information                             |
| Ambient temperature                             | -25 °C ... 70 °C   |
| Product weight                                  | 22 g   |
| Pneumatic connection 1                          | Push-in sleeve CQ-28   |
| Pneumatic connection 2                          | Push-in sleeve CQ-28   |
| Note on materials                               | RoHS compliant   |
| Blanking plug material                          | POM  |