

# Barbed tubing connector RTU-PK-2/3

Part number: 19542

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal width	1.5 mm
Operating pressure for entire temperature range	-0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating pressure for entire temperature range	-13.775 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Pneumatic connection 1	for pneumatic tubing outside diameter 4 mm
Pneumatic connection 2	for pneumatic tubing outside diameter 3 mm
Ambient temperature Fahrenheit	32 °F ... 140 °F
Note on materials	RoHS compliant
Housing material	Brass