

Clevis foot LBN-32

Part number: 195860

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|---|
| Size | 32 |
| Mounting position | Any |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper are excluded from use. Circuit boards, lines, electrical push-in connectors and coils are excluded |
| Ambient temperature | -40 °C ... 150 °C |
| Product weight | 110 g |
| Note on materials | RoHS compliant |
| Mounting material | Steel Galvanized |
| Bolt material | Steel Galvanized |
| Fuse material | Spring steel, galvanized |