

Clevis foot CRLBN-40

Part number: 195867

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	40
Mounting position	Any
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-40 °C ... 150 °C
Product weight	185 g
Note on materials	RoHS compliant
Mounting material	high-alloy stainless steel
Bolt material	high-alloy stainless steel
Fuse material	high-alloy stainless steel