

Mounting plate VN-T6-BP-NRH

Part number: 196956

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|----------------------------------|
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C ... 60 °C |
| Max. tightening torque | 0.8 Nm |
| Product weight | 12.4 g |
| Type of mounting | With through-hole With H-rail |
| Note on materials | RoHS-compliant |
| Plate material | PA-reinforced |
| Gate valve material | POM |