

# Plastic tubing PFAN-12X1,75-NT

Part number: 197065

FESTO



 General operating condition

## Data sheet

Feature	Value
Outside diameter	12 mm
Bending radius relevant for flow rate	165 mm
Inside diameter	8.4 mm
Min. bending radius	29 mm
Application note	Tubing without printing
Symbol	00997424
Operating pressure for entire temperature range	-0.095 MPa ... 0.7 MPa
Operating pressure for entire temperature range	-0.95 bar ... 7 bar
Operating pressure for entire temperature range	-13.775 psi ... 101.5 psi
Temperature-dependent operating pressure	-0.095 MPa ... 1.6 MPa
Temperature-dependent operating pressure	-0.95 bar ... 16 bar
Temperature-dependent operating pressure	-13.775 psi ... 232 psi
Information on operating pressure	Water vapor: 0 - 0.15 MPa, 0 - 1.5 bar, 0 - 22 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) Water vapor
Material fire test	UL94 V-0
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
Note on temperature of medium	Water vapor: max. 120 °C
Ambient temperature	-20 °C ... 150 °C
Product weight by length	0.125 kg/m
Pneumatic connection	For plug connection outside diameter 12 mm
Color	nature
Shore hardness	D 60 +5
Note on materials	RoHS compliant
Material of pneumatic tubing	PFA