

# Manifold block MHP1-P8-2

Part number: 197200

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                  | Value  |
|--|--|
| Max. no. of valve positions              | 8  |
| Operating pressure                       | 0 bar ... 8 bar  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                   | VDMA24364-B2-L   |
| Ambient temperature                      | -10 °C ... 60 °C   |
| Sub-base mounting type                   | With through-hole  |
| Pneumatic valve mounting type            | With internal thread   |
| Pneumatic connection 1                   | M7   |
| Material of sub-base                     | Wrought aluminum alloy   |