

Clevis foot CRLMC-50

Part number: 197322

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|---|
| Size | 50 |
| Based on norm | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Mounting position | Any |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -40 °C ... 80 °C |
| Product weight | 256 g |
| Note on materials | RoHS-compliant |
| Mounting material | Electropolished High-alloy steel |
| Material of bearing | Polymer |