

Clevis foot CRLMC-80

Part number: 197324

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	80
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Mounting position	Any
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 80 °C
Product weight	483 g
Note on materials	RoHS compliant
Mounting material	Electropolished High-alloy steel
Material of bearing	Polymer