

Manifold MHA2-PR10-3-M5

Part number: 197451

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Max. no. of valve positions	10
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Sub-base mounting type	With through-hole With DIN rail
Pneumatic valve mounting type	With internal thread
Pneumatic connection 1/33	M7
Pneumatic connection 2	M5
Pneumatic connection 3/11	M7
Material of sub-base	Wrought aluminum alloy