

# Pneumatic muffler UO-1/8

Part number: 197583

FESTO



[General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
Structural design	Pneumatic muffler, open
Symbol	00991473
Operating pressure	0 MPa ... 0.8 MPa
Operating pressure	0 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	5 g
Pneumatic connection	G1/8
Cushioning insert material	PE
Material of screwed plug	PE
Note on materials	RoHS-compliant