

Spiral plastic tubing PUN-6X1-S-6-BL

Part number: 197592

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Working length	6 m
Outside diameter	6 mm
Block length	1.214 m
Inside diameter	4 mm
Winding diameter	46 mm
Number of windings	168
Temperature-dependent operating pressure	-0.095 MPa ... 1 MPa
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Temperature-dependent operating pressure	-13.775 psi ... 145 psi
Certification	TÜV
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C ... 60 °C
Product weight	350 g
Pneumatic connection	For plug connection outside diameter 6 mm For barbed fitting, inside diameter 4 mm, with union nut For barbed fitting, inside diameter 4 mm
Color	Blue
Shore hardness	D 52 +/-3
Material of pneumatic tubing	TPE-U(PU)