

# Spiral plastic tubing PUN-12X2-S-1-SW

Part number: 197614

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Working length	1 m
Outside diameter	12 mm
Block length	0.32 m
Inside diameter	8 mm
Winding diameter	95 mm
Number of windings	9
Temperature-dependent operating pressure	-0.095 MPa ... 1 MPa
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Temperature-dependent operating pressure	-13.775 psi ... 145 psi
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C ... 60 °C
Product weight	200 g
Pneumatic connection	For plug connection outside diameter 12 mm
Color	Black
Shore hardness	D 52 +/-3
Material of pneumatic tubing	TPE-U(PU)