

# Spiral plastic tubing PPS-4-7,5-1/4-BL

Part number: 19798

FESTO



 General operating condition

## Data sheet

Feature	Value
Working length	7.5 m
Outside diameter	6.3 mm
Block length	0.34 m
Inside diameter	4.7 mm
Winding diameter	75 mm
Number of windings	44
Temperature-dependent operating pressure	-0.95 bar ... 21.2 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C ... 80 °C
Nominal tightening torque	11 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	249 g
Pneumatic connection 1	External thread G1/4
Pneumatic connection 2	External thread G1/4
Color	Blue
Material of connecting thread	Brass
Note on materials	RoHS-compliant
Antikink device material	Steel Galvanized
Material of pneumatic tubing	PA12-P