

Motor flange EAMF-A-38A-40P

Part number: 1984478

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-10 °C ... 60 °C
Product weight	56 g
Interface code, motor in	40P
Interface code, coupling housing	38A.2
Note on materials	RoHS compliant