

# Union nut MCK-PK-13

Part number: 206504

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	Internal thread M22x1
Operating pressure for entire temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Operating pressure for entire temperature range	-13.775 psi ... 174 psi
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection 1	for barbed connector I.D. 13 mm with union nut
Material of union nut	Wrought aluminum alloy, anodized
Note on materials	RoHS-compliant