

Distributor block FR-8-1/8

Part number: 2077

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Nominal width | 8.6 mm |
| Mounting position | Any |
| Operating pressure for entire temperature range | 0 bar ... 16 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Nominal tightening torque | 12.5 Nm |
| Tolerance for nominal tightening torque | ± 20% |
| Product weight | 135 g |
| No. of outlets | 8 |
| No. of supply lines | 1 |
| Pneumatic connection 1 | Internal thread G3/8 |
| Pneumatic connection 2 | Internal thread G1/8 |
| Note on materials | RoHS-compliant |
| Housing material | Die-cast aluminum |