

Rotary distributor GF-1/4

Part number: 2094

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Nominal width | 11.5 mm |
| Mounting position | Any |
| Operating pressure for entire temperature range | -0.095 MPa ... 1 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 145 psi |
| Standard flow rate 1-2.1 (6->0) | 2932 l/min |
| Standard flow rate 1-2.X open (6->0) | 2977 l/min |
| Standard nominal flow rate 1.1-2.1 | 1792 l/min |
| Max. rotational speed | 300 rpm |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 250 g |
| Pneumatic connection 1 | External thread G1/4 |
| Pneumatic connection 2 | Internal thread G1/4 |
| Note on materials | RoHS-compliant |
| Housing material | Wrought aluminum alloy |
| Shaft material | High-alloy steel |