

Union nut MCK-PK-3-KU

Part number: 211289

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	Internal thread M6x0.75
Operating pressure for entire temperature range	0 MPa ... 1 MPa
Operating pressure for entire temperature range	0 bar ... 10 bar
Operating pressure for entire temperature range	0 psi ... 145 psi
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection 1	for pneumatic tubing outside diameter 4 mm For barbed fitting, inside diameter 3 mm, with union nut
Material of union nut	POM
Note on materials	RoHS compliant