

Union nut MCK-PK-3-KU

Part number: 211289

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Size | Internal thread M6x0.75 |
| Operating pressure for entire temperature range | 0 MPa ... 1 MPa |
| Operating pressure for entire temperature range | 0 bar ... 10 bar |
| Operating pressure for entire temperature range | 0 psi ... 145 psi |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Pneumatic connection 1 | for pneumatic tubing outside diameter 4 mm For barbed fitting, inside diameter 3 mm, with union nut |
| Material of union nut | POM |
| Note on materials | RoHS-compliant |