

# Union nut MCK-PK-4-KU

Part number: 211291

FESTO



 [General operating condition](#)

## Data sheet

| Feature   | Value  |
|---|--|
| Size  | Internal thread M10x1  |
| Operating pressure for entire temperature range | 0 MPa ... 1 MPa  |
| Operating pressure for entire temperature range | 0 bar ... 10 bar   |
| Operating pressure for entire temperature range | 0 psi ... 145 psi  |
| LABS (PWIS) conformity                          | VDMA24364-B2-L   |
| Ambient temperature                             | -10 °C ... 60 °C   |
| Pneumatic connection 1                          | For pneumatic tubing outside diameter 6 mm<br>For barbed fitting, inside diameter 4 mm, with union nut |
| Material of union nut                           | POM  |
| Note on materials                               | RoHS-compliant   |