

# Quick coupling plug KS4-N-9

Part number: 2153

FESTO



 General operating condition

## Data sheet

Feature	Value
Nominal width	7 mm
Operating pressure for entire temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Operating pressure for entire temperature range	-13.775 psi ... 174 psi
Normal nominal flow rate (normalized to DIN 1343)	711 l/min ... 1134 l/min
Nominal flow rate standardized according to ISO 8778	770.7 l/min ... 1229.3 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	18 g
Pneumatic connection 1	Barbed hose fitting 9 mm
Note on materials	RoHS-compliant
Information on materials	Brass, nickel-plated