

Pivot pin kit DAMT-V1-63-A

Part number: 2214971

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|---|
| Size | 63 |
| Based on norm | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper are excluded from use. Circuit boards, lines, electrical push-in connectors and coils are excluded |
| Ambient temperature | -40 °C ... 150 °C |
| Max. load capacity | 4 kN |
| Product weight | 910.6 g |
| Note on materials | RoHS-compliant |
| Material of screws | Steel Galvanized |
| Trunnion flange material | Steel, galvanized |
| Clamping piece material | Steel, galvanized |
| Rod material | High-alloy stainless steel |