

Clamping sleeve EAMH-50-8-C13.6

Part number: 2428480

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	50
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	0.4 kgmm ²
Product weight	16 g
Note on materials	RoHS-compliant