

Clamping sleeve EAMH-145-25-C34

Part number: 2429593

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------|------------------------|
| Size | 145 |
| Mounting position | Any |
| Max. rotational speed | 4000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -10 °C ... 60 °C |
| Mass moment of inertia | 28.1 kgmm ² |
| Product weight | 165 g |
| Note on materials | RoHS-compliant |