

Sealing ring NPAS-C1-R-G18-P-FD-P10

Part number: 2652516

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Pack size	10
Mounting position	Any
Operating pressure for entire temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Operating pressure for entire temperature range	-13.775 psi ... 174 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) Water vapor
Information on operating and pilot media	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B2-L
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C ... 120 °C
Nominal tightening torque	6.5 Nm
Tolerance for nominal tightening torque	±10%
Product weight	0.02 g
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Seals material	PEEK