

Flange mounting EAHH-V2-40-R1

Part number: 2827588

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	40
Based on norm	ISO 15552
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
Max. load capacity	3 kN
Product weight	275 g
Note on materials	RoHS compliant
Plate material	high-alloy stainless steel
Material of screws	high-alloy stainless steel