

# Bellows kit EADB-V2-50-S401-500

Part number: 2828843

FESTO



 General operating condition

## Data sheet

Feature	Value
Outside diameter	93 mm
Size	50
Stroke range	401 mm ... 500 mm
Piston rod extension	119 mm
Design	Round
Mounting position	Any
Structural design	With ducted exhaust
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media resistance	Dust Chips Oils Grease Petrol
Degree of protection	IP65 As per IEC 60529
Ambient temperature	-10 °C ... 80 °C
Moving mass	305 g
Product weight	402 g
Type of mounting	Push-fitted With threaded pin
Pneumatic connection	G1/4
Note on materials	RoHS compliant
Adaption parts material	Wrought aluminum alloy Anodized
Seals material	NBR
Bellows material	NBR
Threaded pin material	high-alloy stainless steel