

Manifold block MRS-2

Part number: 2844247

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	2
Max. no. of valve positions	2
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Max. tightening torque for valve mounting	2.5 Nm
Max. tightening torque for wall mounting	4 Nm
Product weight	365 g
Pneumatic connection 1	G3/8
Note on materials	RoHS-compliant
Material of sub-base	Wrought aluminum alloy