

# Union nut MCK-PK-4

Part number: 2965

FESTO



 [General operating condition](#)

## Data sheet

| Feature   | Value  |
|---|--|
| Size  | Internal thread M10x1  |
| Operating pressure for entire temperature range | -0.095 MPa ... 1.2 MPa   |
| Operating pressure for entire temperature range | -0.95 bar ... 12 bar   |
| Operating pressure for entire temperature range | -13.775 psi ... 174 psi  |
| Corrosion resistance class (CRC)                | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity                          | VDMA24364-B2-L   |
| Ambient temperature                             | -10 °C ... 60 °C   |
| Pneumatic connection 1                          | For pneumatic tubing outside diameter 6 mm<br>For barbed fitting, inside diameter 4 mm, with union nut |
| Material of union nut                           | Wrought aluminum alloy, anodized   |
| Note on materials                               | RoHS-compliant   |