

Union nut MCK-PK-9

Part number: 2967

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Size | Internal thread M16x1 |
| Operating pressure for entire temperature range | -0.095 MPa ... 1.2 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 12 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 174 psi |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Pneumatic connection 1 | For barbed fitting, inside diameter 9 mm, with union nut |
| Material of union nut | Wrought aluminum alloy, anodized |
| Note on materials | RoHS compliant |