

Connecting cable KMC-1-230AC-2,5

Part number: 30932

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Maritime classification | See certificate |
| Type of mounting | On air solenoid valve with M3 central screw |
| Mounting position | Any |
| Product weight | 170 g |
| Electrical connection | Socket Type A |
| Nominal operating voltage AC | 230 V |
| Reverse polarity protection | for all electrical connections |
| Protective earth connection | Available |
| Cable length | 2.5 m |
| Cable diameter | 6 mm |
| Cable design | 3 x 0.75 mm ² |
| Degree of protection | IP67 As per IEC 60529 |
| Ambient temperature | -20 °C ... 80 °C |
| CE marking (see declaration of conformity) | As per EU low voltage directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions To UK instructions for electrical equipment |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Material of cable sheath | PVC |
| Housing material | PC |
| Material of pin contacts | Bronze |