

# Rod clevis SG-M8

Part number: 3111

FESTO



 [General operating condition](#)

## Data sheet

| Feature  | Value   |
|--|---|
| Size   | M8  |
| Conforms to standard                               | ISO 8140  |
| Threaded connection                                | Internal thread M8  |
| Corrosion resistance class (CRC)                   | 1 - Low corrosion stress  |
| LABS (PWIS) conformity                             | VDMA24364-B2-L  |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper are excluded from use. Circuit boards, lines, electrical push-in connectors and coils are excluded |
| Ambient temperature                                | -40 °C ... 150 °C   |
| Product weight                                     | 53 g  |
| Note on materials                                  | RoHS compliant  |
| Bolt material                                      | Steel<br>Galvanized   |
| Clevis material                                    | Steel<br>Galvanized   |
| Nut material                                       | Steel<br>Galvanized   |